

# Product data sheet

Specifications



Unica Top/Class - rocker switch - 2 poles 1-way - 16 AX 250 VAC - 2 m - graph.

MGU50.262.12SZ

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

## Main

Range Of Product	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	Switch
Device Presentation	Mechanism with fixing frame
Technology Type	Electromechanical
Switch Function	2-pole 1-way
Number Of Rocker	1
Device Application	Light control
Colour Tint	Graphite

## Complementary

Rated Current	16 AX
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Electrical Durability	5000 cycles
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening Distance	> 3 mm
Actuator	Rocker
Number Of Modules	2 modules
Pilot Light	LED, colour: amber, current consumption: 0.15 mA, temperature rise: 15 °C
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm² rigid cable 0...4 mm² flexible cable
Material	Zamak: fixing frame
Marking	ON
Fixing Mode	Long claws
Width	70.9 mm
Height	70.9 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	33 mm
Embedding Depth	21 mm
Net Weight	0.069 kg
Ambient Air Temperature For Operation	25...35 °C
Ambient Air Temperature For Storage	0...50 °C
Standards	EN 60669-1 EMC directive LV directive

## Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Environmental Characteristic	Window-cleaning fluid UV resistant Oil Acetone Bleach Alcohol Liquid soap Petrol

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	70.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.5 cm
Package 2 Width	20.0 cm
Package 2 Length	22.5 cm
Package 2 Weight	800.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	50
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	4.411 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations