

Product data sheet

Specifications



Unica Top/Class - 2 RJ45 socket (S-One) - 2x1 m - Cat.6, FTP - graph.

MGU50.2626.12Z

⚠ Discontinued on: Apr 28, 2014

⚠ Discontinued

Main

Range	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	Data socket
Device Presentation	Mechanism with fixing frame
Colour Tint	Graphite
Data Socket Type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided Equipment	Protective flap Label holder

Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	2 x 1 modules
Socket Number	2
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/FTP
Organization Of Wire	Shielded twisted pair
Connections - Terminals	Click
Fixing Mode	Long claws
Installation Direction	Straight
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover Zamak: fixing frame
Depth	36 mm
Width	70.9 mm
Height	70.9 mm
Embedding Depth	25 mm
Net Weight	0.098 kg

Environment

Ip Degree Of Protection	IP40
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	UV resistant Liquid soap Alcohol Oil Petrol Window-cleaning fluid Acetone Bleach
Standards	ISO 8877

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.5 cm
Package 1 Length	3.6 cm
Package 1 Weight	100 g

Contractual warranty

Warranty	18 months
-----------------	-----------