

# Product data sheet

Specifications



## Unica KNX - infrared pushbutton - 2-way - 10 A, 250 VAC - 2 m - graphite

MGU50.532.12

 **Discontinued on:** Dec 31, 2017

 **Discontinued**

### Main

Range	Unica
Aesthetic Name	Unica KNX
Product Or Component Type	Switch
Device Application	Control
Device Presentation	Mechanism with zamak fixing frame + long claws
Cover Plate Colour Tint	Graphite

### Complementary

Rated Current	10 A at 250 V AC 50/60 Hz
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Number Of Modules	2 modules
Switch Function	2-way
Contacts Type And Composition	2 NO
Opening Distance	> 3 mm
Transmission Support Medium	Infrared
Actuator	Push-button
Pilot Light	LED, colour: blue, current consumption: 1 mA, temperature rise: 15 °C
Connections - Terminals	Screwless terminals
Cable Cross Section	2.5 mm² flexible cable 2.5 mm² rigid cable
Fixing Mode	Claws

### Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	-5...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Bleach
	Liquid soap
	Alcohol
	Petrol
	Window-cleaning fluid
	Oil
	UV resistant
	Acetone
Standards	LV directive
	EMC directive

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	0.142 kg

## Contractual warranty

Warranty	18 months
----------	-----------