



has not been replaced. Please contact your customer care center for more information.

Main

Range	Unica
Aesthetic name	Unica KNX
Product or component type	Room temperature control unit
Device presentation	Mechanism with zamak fixing frame + long claws
Colour tint	Ivory

Complementary

[Ue] rated operational voltage	230 V AC +/- 10 % at 50/60 Hz
Number of modules	2 modules
Device composition	4 buttons Display
Clamping connection capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Contacts type and composition	1 C/O
Connections - terminals	Screwless terminals
Information displayed	Time Operating mode Day Temperature
Status LED	Programming LED
Programmable temperature	No
Temperature setting range	0...40 °C
Measurement accuracy	± 1 K
Fixing mode	Long claws
Minimum mounting height	1.5 m
Depth	39 mm
Embedding depth	26 mm

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-5...45 °C
Environmental characteristic	Window-cleaning fluid

Alcohol
Petrol
Ammonia
Bleach
Liquid soap
UV resistant
Oil
Acetone

Environmental health and issues	Halogen free
Standards	EMC directive LV directive

Contractual warranty

Warranty	18 months
----------	-----------
