



Main

Range	Unica
Aesthetic name	Unica
Product or component type	Emergency light
Device presentation	Mechanism with zamak fixing frame
[Ue] rated operational voltage	230 V AC +/- 10 % at 50 Hz
Number of modules	2 modules
Fixing mode	Clip-in

Complementary

Condition of use	Battery and bulb cannot be replaced
Light block colour	Green
Bulb type	LED
Bulb lifespan	400 h
Illuminance	25 cm: 45 lux
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Charging time	24 h
Electrical durability	500 cycles
Material	Transparent plastic: mechanism cover Zamak: fixing frame
Standards	EMC directive LV directive EN 60598-2-22 UNE 20062-93 UNE 60598-2-22
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	33 mm

Depth	44 mm
Width	45 mm
Height	45 mm

Environment

IP degree of protection	IP20
Environmental characteristic	Oil Ammonia Window-cleaning fluid Bleach Liquid soap Petrol Alcohol Acetone UV resistant
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------