

Product data sheet

Specifications



UNICA - 15A, Switched Socket - White

MGU5_018_WE

 **Discontinued on:** Dec 15, 2022

 **Discontinued**

Main

Range Of Product	Unica
Device Application	Power supply
Product Or Component Type	Switched socket
Device Presentation	Mechanism with fixing frame
Outlet Poles Configuration	2P + E
Outlet Standard	European

Complementary

Device Mounting	Flush
Mounting Support	Wall mounted
Socket Number	1
Pilot Light	Red neon indicator
Rated Current	15 A
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50 Hz
Load Type	Resistive
Number Of Modules	2 modules
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Colour Tint	White
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	L N Earth
Tightening Torque	0.4 N.m
Clamping Connection Capacity	2.5 mm² for rigid cable(s) 2.5 mm² for stranded cable(s) 2.5 mm² for flexible cable(s)
Material	PC (polycarbonate): grid plate PC (polycarbonate): base
Projecting Depth	8 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Quantity Per Set	Set of 5
Type Of Packing	Polybag
Embedding Depth	35 mm
Depth	15 mm
Width	81 mm
Height	83 mm
Net Weight	0.073 kg

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Standards	BS 546 BS 7671
Environmental Characteristic	Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.3 cm
Package 1 Width	8.1 cm
Package 1 Length	1.5 cm
Package 1 Weight	73.0 g