



Main

Range of product	Unica
Device application	Power supply
Product or component type	Switched socket
Device presentation	Mechanism with fixing frame
Outlet poles configuration	2 x 2P + E
Outlet standard	British

Complementary

Device mounting	Flush
Mounting support	Wall mounted
Outlet standard description	3 pins
Pilot light	Neon indicator red
Rated current	13 A 250 V AC 50 Hz
Load type	Resistive
Number of gangs	2 gangs
Fixing mode	By screw M3.5
Fixing center	120.6 mm
Colour tint	Tabacco
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	Earth N L
Tightening torque	0.4 N.m
Clamping connection capacity	2 x 4 mm ² rigid 2 x 4 mm ² stranded 2 x 4 mm ² flexible 3 x 2.5 mm ² rigid 3 x 2.5 mm ² stranded 3 x 2.5 mm ² flexible
Material	Grid plate : PC (polycarbonate) Base : PC (polycarbonate)
Projecting depth	8 mm
Quantity per set	10 polybag

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding depth	35 mm
Depth	15 mm
Width	140 mm
Height	83 mm
Product weight	0.12 kg

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
IK degree of protection	IK01
IP degree of protection	IP20
Standards	SASO 2203 BS 1363 BS 7671
Environmental characteristic	Indoor use