


Product data sheet

Specifications



Unica - 1 S.O. (lid) - complete product - 2P+E, DE - 2 m - white - IP44

MGU61.037.18

 **Discontinued on:** Dec 31, 2023

 **Discontinued**

Main

Range	Unica
Product Or Component Type	Socket-outlet
Aesthetic Name	Unica (standard aesthetic)
Device Presentation	Complete product
Device Mounting	Flush
Socket Number	1
Outlet Poles Configuration	2P + E
Outlet Standard	Schuko
Outlet Standard Description	Side earth (TTL)
Socket Additional Information	With earth (TTL) + security cover
Rated Current	16 A

Complementary

Device Application	Power supply
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003)
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	Polyamide 6: mechanism cover ASA + PC: fixing frame ASA + PC: cover frame
Surface Finish	Brilliant
Quantity Per Set	Set of 1 box

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding Depth	30 mm
Depth	40 mm
Width	90 mm
Height	80 mm
Net Weight	0.088 kg
Surface Treatment	Untreated

Environment

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP44
Environmental Characteristic	Window-cleaning fluid Liquid soap Bleach Petrol Alcohol Acetone UV resistant Oil

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	8.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	85.800 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12.000 cm
Package 2 Width	12.500 cm
Package 2 Length	18.500 cm
Package 2 Weight	497.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	40
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.349 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations