

Product data sheet

Specifications



Unica Plus - 2 complete S.O. , UK - 4 m - ivory/mink

MGU63.063.574

⚠ Discontinued on: Apr 5, 2017

⚠ End-of-service on: Sep 1, 2017

⚠ Discontinued

Main

Range	Unica
Product Or Component Type	Socket-outlet
Aesthetic Name	Unica Plus
Device Presentation	Complete mechanism
Device Mounting	Flush
Socket Number	2
Outlet Standard	British
Socket Additional Information	Unearthed
Rated Current	16 A

Complementary

Device Application	Power supply
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	4 modules
Fixing Mode	Short claws
Colour Tint	Ivory
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm² - cable stiffness: flexible 0...4 mm² - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	ASA + PC: mechanism cover ABS (acrylonitrile butadiene-styrene): cover frame
Quantity Per Set	Set of 1 box
Embedding Depth	30 mm
Depth	33 mm
Width	90.21 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	122.9 mm
Net Weight	0.1146 kg

Environment

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Liquid soap Bleach Alcohol Oil Window-cleaning fluid UV resistant Acetone Petrol

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.25 cm
Package 1 Width	9 cm
Package 1 Length	4.75 cm
Package 1 Weight	119 g

Contractual warranty

Warranty	18 months
----------	-----------