

# Product data sheet

Specifications



## Unica Plus - 2 complete S.O. - 2P+E, UK - 4 m - white

MGU63.067.18

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

### Main

Range	Unica
Product Or Component Type	Socket-outlet
Aesthetic Name	Unica Plus
Device Presentation	Complete mechanism
Device Mounting	Flush
Socket Number	2
Outlet Poles Configuration	2P + E
Outlet Standard	British
Outlet Standard Description	Side earth
Socket Additional Information	Side earth
Rated Current	16 A

### Complementary

Device Application	Power supply
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	4 modules
Fixing Mode	Short claws
Colour Tint	White
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm <sup>2</sup> - cable stiffness: flexible 0...4 mm <sup>2</sup> - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	ASA + PC: mechanism cover ASA + PC: cover frame
Quantity Per Set	Set of 1 box
Embedding Depth	30 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	33 mm
Width	90.21 mm
Height	122.9 mm
Net Weight	0.128 kg

## Environment

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	UV resistant Alcohol Bleach Petrol Acetone Window-cleaning fluid Oil Liquid soap

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	9 cm
Package 1 Length	12.3 cm
Package 1 Weight	119 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	11.8 cm
Package 2 Width	17.2 cm
Package 2 Length	25 cm
Package 2 Weight	595 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	20
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2380 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations