



Main

| | |
|-------------------------------|--------------------|
| Range | Unica |
| Device application | Power supply |
| Product or component type | Socket-outlet |
| Aesthetic name | Unica Plus |
| Device presentation | Complete mechanism |
| Socket number | 2 |
| Outlet poles configuration | 2P + E |
| Outlet standard | British |
| Socket additional information | Side earth |
| Outlet standard description | Side earth |

Complementary

| | |
|--------------------------------|---|
| Rated current | 16 A, 250 V AC |
| Network frequency | 50/60 Hz |
| Number of modules | 4 modules |
| Fixing mode | Short claws |
| Colour tint | Ivory |
| Connections - terminals | Screw terminals |
| Cable cross section | 0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid |
| Minimum load breaking capacity | 100 operations 1.25 In and 1.1 Un, cos phi: 0.6 |
| Electrical durability | 10000 cycles (cos phi: 0.8) |
| Insulation resistance | > 5 MOhm @500 V |
| Dielectric strength | 2000 V |
| Material | Cover frame : ABS (acrylonitrile butadiene-styrene) Mechanism cover : ASA + PC |
| Quantity per set | Box : set of 1 |
| Embedding depth | 30 mm |

| | |
|----------------|----------|
| Depth | 33 mm |
| Width | 90.21 mm |
| Height | 122.9 mm |
| Product weight | 0.128 kg |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | 15...30 °C |
| Ambient air temperature for storage | 0...35 °C |
| IK degree of protection | IK01 |
| IP degree of protection | IP20 |
| Environmental characteristic | Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid |
| Environmental health and issues | Halogen free |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0610 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|