



Main

Range	Unica
Device application	Power supply
Product or component type	Socket-outlet
Aesthetic name	Unica Plus
Device presentation	Complete mechanism
Socket number	2
Outlet poles configuration	2P + E
Outlet standard	British
Socket additional information	In pin pack Side earth
Outlet standard description	Side earth

Complementary

Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Number of modules	4 modules
Fixing mode	Short claws
Colour tint	White
Connections - terminals	Screw terminals
Cable cross section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Cover frame : ABS (acrylonitrile butadiene-styrene) Mechanism cover : ASA + PC
Quantity per set	Plastic bag and cardboard with eurohole : set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding depth	30 mm
Depth	33 mm
Width	90.21 mm
Height	122.9 mm
Product weight	0.128 kg

Environment

Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0610 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------