



### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Top
Number of gangs	2 gangs horizontal
Fixing mode	Clip-in
Cover frame colour tint	Wengue
Decoration colour	Aluminium

### Complementary

Material	ASA + PC decorative frame ASA + PC intermediate part
Standards	EN 60669-1
Height	80 mm
Width	161 mm
Depth	14 mm
Distance between centers	71 mm
Product weight	0.064 kg
Market segment	Residential Small commercial

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Ammonia Alcohol Oil Acetone Window-cleaning fluid

Petrol  
UV resistant  
Bleach  
Liquid soap

---

Environmental health and issues	Halogen free
---------------------------------	--------------

---

### Offer Sustainability

---

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---