



Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Top
Number of gangs	2 gangs horizontal
Fixing mode	Clip-in
Cover frame colour tint	Cherry tree
Decoration colour	Graphite

Complementary

Material	ASA + PC decorative frame ASA + PC intermediate part
Standards	EN 60669-1
Height	80 mm
Width	161 mm
Depth	14 mm
Distance between centers	71 mm
Product weight	0.064 kg
Market segment	Small commercial Residential

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Petrol Liquid soap UV resistant Bleach Alcohol

Acetone
Oil
Window-cleaning fluid
Ammonia

Environmental health and issues	Halogen free
---------------------------------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Product environmental profile	Available Product Environmental Profile
-------------------------------	--

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
