



### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Plus
Number of gangs	2 gangs horizontal
Fixing mode	Clip-in
Cover frame colour tint	Bright chrome
Decoration colour	White

### Complementary

Material	ASA + PC decorative frame ASA + PC intermediate part
Standards	EN 60669-1
Height	80 mm
Width	161 mm
Depth	14 mm
Distance between centers	71 mm
Product weight	0.09 kg
Market segment	Residential Small commercial

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap

Oil  
Petrol  
UV resistant  
Window-cleaning fluid

---

Environmental health and issues      Halogen free

---

### Offer Sustainability

---

Sustainable offer status      Green Premium product

---

RoHS (date code: YYWW)      Compliant - since 1834 - Schneider Electric declaration of conformity  
[Schneider Electric declaration of conformity](#)

---

REACH      Reference not containing SVHC above the threshold  
[Reference not containing SVHC above the threshold](#)

---

Product environmental profile      Available  
[Product Environmental Profile](#)

---

Product end of life instructions      Need no specific recycling operations

---

### Contractual warranty

---

Warranty period      18 months

---