



Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Top
Number of gangs	3 gangs vertical
Fixing mode	Clip-in
Cover frame colour tint	Beryl blue
Decoration colour	Aluminium

Complementary

Material	ASA + PC: decorative frame ASA + PC: intermediate part Zamak: cover frame
Standards	EN 60669-1
Height	232 mm
Width	80 mm
Depth	14 mm
Distance between centers	71 mm
Net weight	0.115 kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Liquid soap Alcohol Bleach UV resistant Petrol Oil

	Window-cleaning fluid Ammonia Acetone
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------