



Main

Range	Unica
Device application	Mounting
Product or component type	Mounting box for mechanism
Aesthetic name	Unica Allegro
Number of modules	4 modules
Number of gangs	1 gang
Fixing mode	By 4 pins
Additional information	Flame resistance 650 °C-30 s Self-extinguishing materials
Box colour tint	White

Complementary

Wiring device mounting	Surface
Cable entry	4 knock-outs
Product compatibility	For rectangular fixing frame
Material	ASA + PC: box
Depth	35 mm
Width	138.5 mm
Height	80 mm
Net weight	0.075 kg

Environment

Standards	UNE 60670-1 RoHS compliant
IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Petrol Bleach

Ammonia
Liquid soap
Oil
UV resistant
Alcohol
Window-cleaning fluid
Acetone

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------