



has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range	Mini Pragma
Product or component type	Enclosure
Enclosure type	Modular enclosure
Nb of 18 mm modules per row	18
Nb of horizontal rows	1
Type of door	Transparent door
Width	376 mm outside:
Height	228 mm outside:
Depth	103 mm outside:

Complementary

Enclosure mounting	Surface
9 mm pitches	36
Total number of 18 mm modules	18
[In] rated current	63 A
Type of rail	35 mm asymmetrical rail
Cable entry	1 bare flange 1 trunking flange
Terminal block function	Earth / neutral
Number of terminal blocks	1 earth (screwed) with 16 outgoing 1 neutral (screwed) with 16 outgoing
Distribution block outgoing	2 x 16 mm ² for earth 2 x 16 mm ² for neutral 6 x 6 mm ² for earth 6 x 6 mm ² for neutral 8 x 10 mm ² for earth 8 x 10 mm ² for neutral
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Front face: white

Door: smoked

Environment

Standards	IEC 60439-3 IEC 60670-24 EN 50102 IEC 529 IEC 60695-2-11
Quality labels	IMQ
Fire resistance	Back part: 750 °C Door: 650 °C Front face: 750 °C
IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

Contractual warranty

Warranty	18 months
----------	-----------
