

Product data sheet

Specifications



Mini Pragma surface enclosure - IP 40 - 3 x 12 modules - smoked transparent door

MIP02312T

⚠ Discontinued on: Jul 25, 2019

⚠ Discontinued

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	3
Type Of Door	Transparent door
Width	268 mm outside:
Height	478 mm outside:
Depth	102 mm outside:

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	24
Total Number Of 18 Mm Modules	36
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Cable Entry	1 bare flange 1 trunking flange
Terminal Block Function	Earth / neutral
Number Of Terminal Blocks	1 earth (screwed) with 20 outgoing 1 neutral (screwed) with 20 outgoing
Distribution Block Outgoers	2 x 16 mm² for earth 2 x 16 mm² for neutral 9 x 10 mm² for earth 9 x 10 mm² for neutral 9 x 6 mm² for earth 9 x 6 mm² for neutral
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Front face: white Door: smoked

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Back part: 750 °C Door: 650 °C Front face: 750 °C
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.2 cm
Package 1 Width	26.8 cm
Package 1 Length	47.8 cm
Package 1 Weight	1.55 kg

Contractual warranty

Warranty	18 months
----------	-----------