

Product data sheet

Specifications



Enclosure, Resi9 MP, surface mounting, 1 row of 6 modules, IP40, white door, no terminal block

MIP10106

Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	6
Nb Of Horizontal Rows	1
Type Of Door	Plain
Width	160 mm outside:
Height	198 mm outside:
Depth	95.5 mm outside:

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	12
Total Number Of 18 Mm Modules	6
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	1 trunking flange 1 bare flange
Terminal Block Function	Without
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	74 mm
Colour	Door: white (RAL 9003) Front face: white (RAL 9003)
Market Segment	Residential

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.6 cm
Package 1 Width	16.0 cm
Package 1 Length	19.8 cm
Package 1 Weight	400.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	18
Package 2 Height	52.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.3 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	120.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	128.8 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations