

Product data sheet

Specifications



Enclosure, Resi9 MP, surface mounting, 3 rows of 12 modules, IP40, white door, no terminal block

MIP10312

Main

| | |
|-----------------------------|-------------------|
| Range | Resi9 |
| Product Name | Resi9 MP |
| Product Or Component Type | Enclosure |
| Enclosure Type | Modular enclosure |
| Nb Of 18 Mm Modules Per Row | 12 |
| Nb Of Horizontal Rows | 3 |
| Type Of Door | Plain |
| Width | 268 mm outside: |
| Height | 478 mm outside: |
| Depth | 102 mm outside: |

Complementary

| | |
|-------------------------------|--|
| Enclosure Mounting | Surface |
| 9 Mm Pitches | 24 |
| Total Number Of 18 Mm Modules | 36 |
| [In] Rated Current | 63 A |
| Type Of Rail | 35 mm asymmetrical rail |
| Mounting Plate Description | Without mounting plate |
| Cable Entry | 1 trunking flange 1 bare flange |
| Terminal Block Function | Without |
| Enclosure Material | Back part: technoplastic Door: technoplastic Front face: technoplastic |
| Internal Depth | 80 mm |
| Colour | Door: white (RAL 9003) Front face: white (RAL 9003) |
| Market Segment | Residential |

Environment

| | |
|----------------|---|
| Standards | IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24 |
| Quality Labels | IMQ |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|---|
| Fire Resistance | Door: 650 °C Back part: 650 °C Front face: 650 °C |
| Ip Degree Of Protection | IP40 |
| Ik Degree Of Protection | IK07 |
| Ambient Air Temperature For Operation | -25...60 °C |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 10.2 cm |
| Package 1 Width | 26.8 cm |
| Package 1 Length | 47.8 cm |
| Package 1 Weight | 1.36 kg |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 4 |
| Package 2 Height | 52.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 5.54 kg |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 64 |
| Package 3 Height | 120.0 cm |
| Package 3 Width | 80.0 cm |
| Package 3 Length | 120.0 cm |
| Package 3 Weight | 100.64 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |