


# Product data sheet

Specifications



## mini Pragma surface enclosure - 3 x 12 modules - smoked door

MIP11312S

 **Discontinued on:** Mar 23, 2020

 **Discontinued**

### Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	3
Type Of Door	Smoked
Width	268 mm outside:
Height	478 mm outside:
Depth	102 mm outside:

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	24
Total Number Of 18 Mm Modules	36
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Cable Entry	1 bare flange 1 trunking flange
Terminal Block Function	Earth
Number Of Terminal Blocks	1 earth (screwed) with 20 outgoing
Distribution Block Outgoers	2 x 16 mm² for earth 9 x 10 mm² for earth 9 x 6 mm² for earth
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Door: smoked Front face: white (RAL 9003)

### Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	Back part: 750 °C Door: 650 °C Front face: 750 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.3 cm
Package 1 Width	27 cm
Package 1 Length	47.8 cm
Package 1 Weight	1.504 kg

## Contractual warranty

Warranty	18 months
----------	-----------