

Product data sheet

Specifications



Enclosure, Resi9 MP, flush mounting, 3 rows of 12 modules, IP40, translucent door, 1 earth terminal block

MIP21312T

Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	3
Type Of Door	Translucid
Width	270 mm wall: 294 mm outside:
Height	478 mm wall: 502 mm outside:
Depth	18 mm outside: 80 mm wall: 98 mm total:

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	24
Total Number Of 18 Mm Modules	36
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	Pre-cutted holes
Terminal Block Function	Earth
Number Of Terminal Blocks	1 earth (screwed) with 20 outgoers
Distribution Block Outgoers	2 x 16 mm² for earth 9 x 10 mm² for earth 9 x 6 mm² for earth
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	76 mm
Colour	Front face: white (RAL 9003) Door: translucid

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Front face: 750 °C Back part: 850 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	29.2 cm
Package 1 Length	50.2 cm
Package 1 Weight	1.899 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	52.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.6 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	64
Package 3 Height	120.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	133.6 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile