

# Product data sheet

Specifications



Enclosure, Resi9 MP, flush mounting, 1 row of 12 modules, IP40, smoked door, 1 earth + 1 neutral terminal blocks

MIP22112S

## Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	1
Type Of Door	Smoked
Width	270 mm wall: 294 mm outside:
Height	228 mm wall: 252 mm outside:
Depth	18 mm outside: 80 mm wall: 98 mm total:

## Complementary

Enclosure Mounting	Flush
9 Mm Pitches	24
Total Number Of 18 Mm Modules	12
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	Pre-cutted holes
Terminal Block Function	Earth / neutral
Number Of Terminal Blocks	1 earth (screwed) with 8 outgoing 1 neutral (screwed) with 8 outgoing
Distribution Block Outgoers	1 x 16 mm² for earth 1 x 16 mm² for neutral 3 x 6 mm² for earth 3 x 6 mm² for neutral 4 x 10 mm² for earth 4 x 10 mm² for neutral
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	76 mm
Colour	Front face: white (RAL 9003) Door: smoked (RAL 9003)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Market Segment	Small commercial Residential
----------------	---------------------------------

## Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.800 cm
Package 1 Width	25.200 cm
Package 1 Length	29.400 cm
Package 1 Weight	874.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	53.000 cm
Package 2 Width	30.700 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.000 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	128
Package 3 Height	120.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	140.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations