

Product data sheet

Specifications

EBExpert MPM-NW, Gateway Only

MPMNW0005045



⚠ Discontinued on: Dec 31, 2017

⚠ Discontinued

Main

Range	EcoStruxure Building Expert
Product Or Component Type	Gateway
Device Application	Building automation systems
Supply	External supply conforming to CSA
Processor Name	ARM9 32-bit at 400 MHz
Battery Type	Lithium

Complementary

Communication Port Protocol	BACnet , Ethernet ,RJ45 ,10/100 Mbit/s CANbus ,125...500 kbit/s
[Us] Rated Supply Voltage	24 V AC 50/60 Hz +/- 15 % 24 V DC +/- 10 %
System Requirements	Google Chrome Internet browser Apple Safari Firefox
Power Consumption In W	1.6 W
Power Consumption In Va	5 VA
Communication Gateway	Ethernet/ZigBee
Memory Capacity	64 MB flash
Mounting Mode	Clip-on
Mounting Support	DIN rail
Height	191 mm
Width	116 mm
Depth	45 mm
Enclosure Material	ABS
Standards	CSA C22.2 ICES-003 CE

Environment

Ambient Air Temperature For Operation	60 °C
Relative Humidity	90 % non-condensing

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	14.1 cm
Package 1 Length	14.1 cm
Package 1 Weight	0.213 kg