

Product data sheet

Specifications



SCHUKO sock.-out., light outl.&LED
light.mod.shut.screw, mocca
metallic, Sys.Des.

MTN2304-6052

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

Main

Range	Merten
Product Name	System Design
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with fixing frame and cover plate

Complementary

Device Mounting	Flush
Fixing Mode	By screws and claws
Device Application	Power supply
Socket Number	1
Outlet Poles Configuration	2P + E
Outlet Standard	Schuko
Outlet Standard	CEE 7/3
Cover Type	With shutter
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Colour Tint	Mocca
Material	Metal
Surface Treatment	Varnished
Surface Finish	Matt
Connections - Terminals	Screwless terminals
Ip Degree Of Protection	IP20
Width	71 mm
Height	71 mm
Depth	42 mm
Standards	DIN 49440

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	7.6 cm
Package 1 Length	7.6 cm
Package 1 Weight	105 g