



### Main

Aesthetic name	Aquadesign
Product or component type	Socket-outlet
Device presentation	Mechanism with central plate
Outlet standard	German
Socket additional information	Shuttered With hinged lid

### Complementary

Outlet poles configuration	2P + E
Wiring device mounting	Flush
Fixing mode	By screws and claws
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Colour tint	White
Colour code	RAL 1013
Connections - terminals	Screwless terminals
Material	Polycarbonate glossy

### Environment

IP degree of protection	IP44
Environmental health and issues	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

---

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---