



### Main

Aesthetic name	Aquadesign
Product or component type	Socket-outlet
Device presentation	Mechanism with central plate
Outlet standard	German
Socket additional information	With hinged lid With label surface Shuttered

### Complementary

Outlet poles configuration	2P + E
Wiring device mounting	Flush
Fixing mode	By screws and claws
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Colour tint	Aluminium
Connections - terminals	Screwless terminals
Material	Polycarbonate glossy
Surface treatment	Varnished

### Environment

IP degree of protection	IP20
Environmental health and issues	Halogen free

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Will be compliant – Date to be confirmed
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

---

Warranty	18 months
----------	-----------

---