

# Product data sheet

## Characteristics

# MTN2313-0325

SCHUKO sock.-out.,hng.lid, indic.lamp&label fld, shut.screwl.act.wht,glos.Sys.M



### Main

Aesthetic name	M-Arc M-Elegance M-Plan M-Plan glass M-Smart M-Star System M
Product or component type	Socket-outlet
Device presentation	Mechanism with central plate
Outlet standard	German
Socket additional information	Shuttered With label surface

### Complementary

Outlet poles configuration	2P + E
Local signalling	With lighting
Wiring device mounting	Flush
Fixing mode	By screws and claws
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Colour tint	Active white glossy
Colour code	RAL 9016
Connections - terminals	Screwless terminals
Material	Polycarbonate glossy
Surface treatment	Antibacterial

### Environment

IP degree of protection	IP20
Environmental health and issues	Halogen free

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1642 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---

REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------