

Product data sheet

Specifications



SCHUKO sock.-out.,hng.lid&label
fld,vari.locks, shut.screwl.
term.anthr. Aq.des.

MTN2316-7214

⚠ Discontinued on: Mar 21, 2018

⚠ Discontinued

Main

Aesthetic Name	Aquadesign
Device Presentation	Mechanism with central plate
Outlet Standard	German
Product Or Component Type	Socket-outlet
Socket Additional Information	With hinged lid Shuttered With label surface Lockable

Complementary

Outlet Poles Configuration	2P + E
Wiring Device Mounting	Flush
Fixing Mode	By screws and claws
Colour Tint	Anthracite (RAL 7024)
Connections - Terminals	Screwless terminals
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	7 cm
Package 1 Length	8.2 cm
Package 1 Weight	0.135 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications