



Main

Aesthetic name	Aquadesign
Product or component type	Socket-outlet
Device presentation	Mechanism with central plate
Outlet standard	German
Socket additional information	Shuttered With hinged lid

Complementary

Outlet poles configuration	2P + E
Wiring device mounting	Flush
Fixing mode	By screws and claws
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Colour tint	Anthracite
Colour code	RAL 7024
Connections - terminals	Screwless terminals
Material	Polycarbonate glossy

Environment

IP degree of protection	IP44
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
