



### Main

|                               |  |
|-------------------------------|--|
| Aesthetic name                | M-Arc<br>M-Elegance<br>M-Plan<br>M-Plan glass<br>M-Smart<br>M-Star<br>System M |
| Product or component type     | Socket-outlet  |
| Device presentation           | Mechanism with central plate   |
| Outlet standard               | German   |
| Socket additional information | Shuttered  |

### Complementary

|                                |                      |
|--------------------------------|----------------------|
| Outlet poles configuration     | 2P + E               |
| Wiring device mounting         | Flush                |
| Fixing mode                    | By screws and claws  |
| [In] rated current             | 16 A                 |
| [Ue] rated operational voltage | 250 V                |
| Colour tint                    | Polar white glossy   |
| Colour code                    | RAL 9010             |
| Connections - terminals        | Screwless terminals  |
| Material                       | Polycarbonate glossy |

### Environment

|                                 |              |
|---------------------------------|--------------|
| IP degree of protection         | IP20         |
| Environmental health and issues | Halogen free |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1426 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available<br><a href="#">Product Environmental Profile</a>  |
| Product end of life instructions | Need no specific recycling operations   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|