

Product data sheet

Specifications



USB charger + socket-outlet, Merten
System Design, 2P + E, 16A,
shutter, screwless terminals,
metallic, stainless steel

MTN2366-6036

Main

Range	Merten
Product Name	System Design
Product Or Component Type	USB charger + socket-outlet

Complementary

Device Presentation	Mechanism with fixing frame and cover plate
Device Mounting	Flush
Socket Number	1
Outlet Poles Configuration	2P + E
Outlet Standard	Schuko
Cover Type	With shutter
Rated Current	16 A
Type Of Usb Power Supply	USB type A + A
Integrated Connection Type	1 socket-outlet 250 V AC, maximum load current: 16 A 2 USB port 5 V DC, maximum load current: 2.4 A
Input Power	12 W
Mounting Support	CEE60 installation box
Ground Lug Position	Straight 0° position
Fixing Mode	By screws and claws
Colour Tint	Stainless steel
Surface Finish	Metallic
Surface Treatment	Painted
Type Of Packing	Box
Ambient Air Temperature For Storage	-20...60 °C
Protection Type	Battery charge protection 1 external fuse Automatic overload protection Against short-circuits Automatic restart after ground fault or main power loss Thermal protection
Ambient Air Temperature For Operation	-5...35 °C
Service Life In Cycles	30000 cycles
Connections - Terminals	Screwless terminals
Number Of Terminals	3

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Cables	2
Clamping Connection Capacity	1.5...2.5 mm² for rigid cable(s) 1.5...2.5 mm² for stranded cable(s)
Material	Thermoplastic PC (polycarbonate): casing
Wire Stripping Length	11 mm
Height	71 mm
Width	71 mm
Depth	44 mm
Embedding Depth	32 mm
Net Weight	0.092 kg
Standards	DIN VDE 0620-1 NEN-EN 50198-2 IEC 60884-1 EN/IEC 60950
Product Certifications	NEMKO CB KEMA-KEUR VDE SEMKO FIMKO
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20

Environment

Environmental Characteristic	Normal environment Indoor use
------------------------------	----------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	110.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	80
Package 2 Height	32.5 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.28 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations