



### Main

Aesthetic name	M-Arc M-Elegance M-Plan M-Plan glass M-Smart M-Star System M
Product or component type	Socket-outlet
Device presentation	Mechanism with central plate
Outlet standard	German

### Complementary

Outlet poles configuration	2P + E
Wiring device mounting	Flush
Fixing mode	By screws and claws
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Colour tint	Aluminium
Connections - terminals	Screwless terminals
Material	Polycarbonate matt
Surface treatment	Varnished

### Environment

IP degree of protection	IP20
Environmental health and issues	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0802 - Schneider Electric declaration of conformity

[Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------