

Product data sheet

Specifications



SCHUKO sock.-out. insrt w. labeling field & shut., polar white, glossy, Sys. M

MTN239919

⚠ Discontinued on: Jan 30, 2013

⚠ Discontinued

Main

Aesthetic Name	System M M-Plan glass M-Elegance M-Star M-Arc M-Smart M-Plan
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with central plate
Outlet Standard	German
Socket Additional Information	Shuttered With label surface

Complementary

Outlet Poles Configuration	2P + E
Wiring Device Mounting	Flush
Fixing Mode	By screws and claws
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V
Colour Tint	Polar white (RAL 9010)
Connections - Terminals	Screwless terminals
Material	Polycarbonate glossy

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	7.1 cm
Package 1 Length	7.1 cm
Package 1 Weight	0.073 kg

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months