

Product data sheet

Specifications



SCHUKO socket - outlet w.label
fld,shutter,screw
term.,white,glossy,SystemM

MTN2402-0344

⚠ Discontinued on: Nov 8, 2017

⚠ Discontinued

Main

Aesthetic Name	M-Star M-Plan glass M-Arc System M M-Plan M-Smart M-Elegance
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with central plate
Outlet Standard	German
Socket Additional Information	With label surface Shuttered

Complementary

Outlet Poles Configuration	2P + E
Wiring Device Mounting	Flush
Fixing Mode	By screws and claws
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V
Colour Tint	White (RAL 1013)
Connections - Terminals	Screw terminal
Material	Polycarbonate glossy

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	7.6 cm
Package 1 Length	7.6 cm
Package 1 Weight	0.094 kg

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months