

Product data sheet

Specifications



SCHUKO sock.-out. w. surge prot.& label fld, shut., screw term., anthr.,Sys.M

MTN2405-0414

⚠ Discontinued on: Dec 31, 2017

⚠ Discontinued

Main

Aesthetic Name	System M M-Arc M-Star M-Smart M-Plan glass M-Elegance M-Plan
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with fixing frame and central plate
Outlet Standard	Schuko
Socket Additional Information	Shuttered

Complementary

Outlet Poles Configuration	2P + E
Marking	With label surface
Number Of Gangs	1 gang
Fixing Mode	By screws and claws
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V
Protection Type	Overvoltage protection
Colour Tint	Anthracite (RAL 7024)
Connections - Terminals	Screw terminal
Material	Polycarbonate matt

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	7.6 cm
Package 1 Length	7.6 cm
Package 1 Weight	0.101 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------