

Product data sheet

Specifications



SCHUKO socket-outlet insert with label.field and ctrl.lamp, anthracite, System M

MTN240914

⚠ Discontinued on: Jul 22, 2011

⚠ Discontinued

Main

Aesthetic Name	System M M-Arc M-Star M-Smart M-Plan glass M-Elegance M-Plan
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with central plate
Outlet Standard	German
Socket Additional Information	With label surface Shuttered

Complementary

Outlet Poles Configuration	2P + E
Local Signalling	With lighting
Wiring Device Mounting	Flush
Fixing Mode	By screws and claws
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V
Colour Tint	Anthracite (RAL 7024)
Connections - Terminals	Screwless terminals
Material	Polycarbonate matt

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	7.1 cm
Package 1 Length	7.1 cm
Package 1 Weight	0.074 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------