



### Main

Range of product	ARGUS presence detector
Range	ARGUS
Product or component type	Presence detector
Colour tint	Polar white
Colour code	RAL 9010
Type of packing	Carton

### Complementary

[Ue] rated operational voltage	220/230 V
Network frequency	50/60 Hz
Input compatibility	Push-buttons and electronic insert
[Ue] rated operational voltage	220/230 V
Input function	1 x external triggering over PL
Output voltage	DALI: 15 V DC
Output current	10 A
Output current	<=30 mA DALI
Type of setting	Time adjustment Light sensitivity adjustable
Control type	Remote control
Function available	Constant light control Master function
Time delay	10 s...30 min
Light intensity adjustment	10...1000 lux
Horizontal detection angle	0...360 °
Detection range	Radius: 7 m
Material	PC (polycarbonate) brilliant
Device mounting	Ceiling
Mounting height	2.5 m

## Environment

IP degree of protection	IP20
Ambient air temperature for operation	0...25 °C
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins