



Main

Range	ARGUS
Product or component type	Movement detector
Load type	Capacitive : : 10 A, 140 μ F - 230 V AC Incandescent lamp : 3000 W - 230 V AC Halogen lamp : 2500 W - 230 V AC
Colour tint	Polar white
Colour code	RAL 9010
Type of packing	Carton

Complementary

[Ue] rated operational voltage	230 V
Network frequency	50 Hz
[Ue] rated operational voltage	230 V
Output current	16 A
Protection type	Creep zone protection
Type of setting	Light sensitivity adjustable Time adjustment
Display type	LED
Time delay	1 s...8 min
Light intensity adjustment	3...1000 lux
Horizontal detection angle	0...360 °
Detection range	Frontal 16 m Lateral 10 m
Material	PC (polycarbonate) with brilliant surface
Device mounting	Ceiling
Mounting height	2.5 m

Environment

IP degree of protection	IP55
-------------------------	------

Ambient air temperature for operation	-20...25 °C
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0845 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details

Contractual warranty

Warranty period	18 months
-----------------	-----------
