



Main

Range of product	ARGUS movement detector
Range	ARGUS
Product or component type	Movement detector
Colour tint	Polar white
Colour code	RAL 9010
Type of packing	Carton

Complementary

[Ue] rated operational voltage	230 V
Network frequency	50 Hz
[Ue] rated operational voltage	230 V
Output current	16 A
Protection type	Creep zone protection
Type of setting	Light sensitivity adjustable Time adjustment
Display type	LED
Time delay	1 s...8 min
Light intensity adjustment	3...1000 lux
Horizontal detection angle	0...220 °
Detection range	Frontal: 12 m Lateral: 12 m
Material	PC (polycarbonate) brilliant
Device mounting	Ceiling Surface
Mounting height	2.5 m

Environment

IP degree of protection	IP55
Ambient air temperature for operation	-20...25 °C

Environmental health and issues	Halogen free
---------------------------------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------