

# Product data sheet

Specifications



Room temperature ctrler 230 V w.  
two way cont.&cen.pl., nickel  
metallic,Sys.Des.

MTN5762-6050

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

## Main

Range	Merten
Product Name	System Design
Product Or Component Type	Thermostat
Device Presentation	Mechanism with fixing frame and cover plate
Colour Tint	Nickel

## Complementary

Device Mounting	Flush
Fixing Mode	By screws
Device Application	Room
Technology Type	Electromechanical
Product Specific Application	Heating and cooling
Function Available	With bimetal sensor With thermal feedback
Hysteresis	0.5 K
Contacts Type And Composition	1 C/O
[In] Rated Current	10 A (on resistive load load) 4 A (on inductive load load) cos phi = 0.6
[Ue] Rated Operational Voltage	230 V
Network Type	AC
Network Frequency	50/60 Hz
Ip Degree Of Protection	IP20
Height	71 mm
Width	71 mm
Depth	41 mm

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	7.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	7.5 cm
Package 1 Weight	99.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	40
Package 2 Height	18.5 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.365 kg