



### Main

Range of product	U.motion
Range compatibility	KNX
Product or component type	Server + touch panel
Device short name	Touch 10
Product destination	U.motion system KNX bus system
Product compatibility	U.motion touch panel Client Touch 7 smartphone tablet PC
Bus type	KNX Ethernet
Operating system	Linux
Display size	10.1 inch
Display colour	65000 colours
Colour tint	Aluminium

### Complementary

Connector type	1 RJ45 4 USB
Integrated connection type	Loudspeaker Microphone
Device mounting	Flush
[Ue] rated operational voltage	100...240 V AC
Maximum power consumption in W	20 W operation
Control type	Touch screen
Display type	TFT
Display resolution	1024 x 600 pixels WSVGA
Illuminating intensity	200 cd
Function available	Visualisation
Memory type	1 GB DDR2 SDRAM

Mounting position	Horizontal
Material	Plastic and metal
Height	343 mm
Width	201 mm
Depth	81 mm
Net weight	2.2 kg

## Environment

Ambient air temperature for operation	0...30 °C
IP degree of protection	IP20 conforming to EN 60529
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)