



### Main

Range of product	KNX
Product or component type	Power supply
Bus type	KNX
Additional information	With integrated choke

### Complementary

Total number of 18 mm modules	4
Mounting support	DIN rail
[Ue] rated operational voltage	110...230 V
Network frequency	50...60 Hz
Output current	320 mA
Local signalling	LED
Input type	Emergency input

### Environment

Environmental health and issues	Halogen free
---------------------------------	--------------

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1426 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---