



Main

Range of product	KNX
Product or component type	Power supply
Bus type	KNX
Additional information	With integrated choke

Complementary

Total number of 18 mm modules	4
Mounting support	DIN rail
[Ue] rated operational voltage	110...230 V
Network frequency	50...60 Hz
Output current	640 mA
Local signalling	LED

Environment

Environmental health and issues	Halogen free
---------------------------------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1426 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------
