



### Main

Range of product	KNX
Product or component type	Access control card reader
Technology type	RFID
Device presentation	Insert with central cover plate
Bus type	KNX
Colour tint	Aluminium brilliant

### Complementary

Fixing mode	By 2 screws
Device mounting	Flush
Number of input channels	2
Number of output channels	2
Mechanical robustness	With anti-theft or dismantling protection
Material	Glass
Height	78 mm
Width	110 mm
Depth	12.1 mm

### Environment

Ambient air temperature for operation	0...45 °C
IP degree of protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications