

Product data sheet

Specifications



U.motion Door station set, 1 unit

MTN6910-0033

⚠ Discontinued on: Jan 23, 2020

⚠ Discontinued

Main

Range Of Product	U.motion
Range Compatibility	KNX
Product Or Component Type	Video door station package
Product Destination	U.motion system IP touch panel
Calling Button	1 bell button
Light Source	LED white illuminated nameplate + bell button (white LED) RAL 1017
Width Compatibility	130 mm
Height Compatibility	331 mm
Depth Compatibility	52 mm

Complementary

Device Composition	IP switching device Weatherproof built-in loudspeaker Video encoder Video camera module Door station
Mounting Mode	Flush-mounted
Fixing Mode	Concealed screws
Surface Finish	Stainless steel
Mechanical Robustness	Vandal-proof
Function Available	Replaceable nameplate from the front Mechanically adjustable colour camera
Connections - Terminals	Screw terminals
Detection Angle	150° horizontal 90° vertical
View Angle Horiz X Vert	60° vertical 70° horizontal
Label Dimensions	64 x 16 mm
Mounting Height	1500...1650 mm
Width	154 mm
Height	355 mm
Depth	2.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Environmental Characteristic	Weatherproof
Ambient Air Temperature For Operation	-20...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30 cm
Package 1 Width	40 cm
Package 1 Length	60 cm
Package 1 Weight	4.3 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
