



Main

Range of product	EasyPact MVS
Product or component type	Control unit
Circuit breaker application	Industrial Standard
Poles description	3P 4P
Protected poles description	3d 3d + N/2 4d
Neutral position	Left
Network type	AC
Trip unit name	ET5S
Trip unit technology	Micro-processor based
Trip unit rating	800...4000 A

Complementary

Network frequency	50/60 Hz
Mounting mode	Fixed
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
Neutral protection setting	Without protection (3d) 0.5 x I _r (3d + N/2) 1 x I _r (4d)
Trip unit protection functions	LSI
Protection type	Instantaneous short-circuit protection Overload protection (long time) Short time short-circuit protection
Fault indication	Overload Short-circuit Internal fault Earth fault
Long time pick-up adjustment type I _r	Adjustable 9 settings
Long time pick-up adjustment range	0.4...1 x I _n
Long time delay adjustment type	Adjustable 9 settings
[Tr] long-time delay adjustment range	0.5...24 s (6 x I _r), accuracy: 0...- 20 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Thermal memory	20 minutes before and after tripping
Short-time pick-up adjustment type lsd	Adjustable 9 settings
[I _{sd}] short-time pick-up adjustment range	1.5...10 x I _r
Short-time delay adjustment type	Adjustable 5 settings
[T _{sd}] short-time delay adjustment range	100...400 ms
Instantaneous pick-up adjustment type li	Adjustable 9 settings
Instantaneous pick-up adjustment range	2...15 x I _n , accuracy: +/- 10 % Off
Zone selective interlocking ZSI	With
Height	200 mm
Width	55 mm
Depth	75 mm
Product weight	0.213 kg

Environment

Ambient air temperature for operation	-5...70 °C
Ambient air temperature for storage	-25...85 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1622 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------