

Product data sheet

Specifications



Genesis - 2 SO - Italian - 2 modules - 10A 250VAC - white

MWD130317517

Main

Product Or Component Type	Socket-outlet
Socket Number	2
Outlet Standard	Italian
Outlet Poles Configuration	2P + E
Device Presentation	Complete product
Colour Tint	White

Complementary

Device Mounting	Flush
Number Of Modules	2 modules
Rated Current	10 A at 250 V AC 50/60 Hz
Fixing Mode	Clip-in
Material	PC (polycarbonate)
Surface Finish	Glossy
Connections - Terminals	Screw clamp terminal
Awg Gauge	AWG 12
Width	113 mm
Height	75 mm
Depth	31 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.9 cm
Package 1 Width	1.4 cm
Package 1 Length	5.6 cm
Package 1 Weight	2670 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations