



### Overview

Model Name	APC Network SurgeArrest, 7 outlet
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Bahamas , Barbados , Belize , Bermuda , Canada , Cayman Islands , Colombia , Costa Rica , Dominican Republic , Ecuador , El Salvador , Guatemala , Haiti , Honduras , Jamaica , Mexico , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

### Output

Number of Outlets	7
Receptacle Style	NEMA 5-15R

### Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	1.83 meters

### Surge Protection and Filtering

Surge energy rating	1680 Joules
EP Joule Rating	3420 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	70.0 dB
Peak Current Normal Mode	13 kA
Peak Current Common Mode	26.0 kA
Data Line Protection	--
Data Lines Protected(multi-line only)	--
Let Through Voltage Rating	40

## Physical

Net Weight	0.91 kg
Maximum Height	51.0 mm
Maximum Width	108.0 mm
Maximum Depth	267.0 mm
Shipping Weight	1.05 kg
Shipping Height	53.0 mm
Shipping Width	184.0 mm
Shipping Depth	324.0 mm
Master Carton Units	12.0
Master Carton Weight	30.0 lbs
SCC Codes	10731304000201
Color	Beige
Units per Pallet	384.0

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

## Conformance

Approvals	CSA , UL 1283 , UL 1363 , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$100000
UL 1449 TVSS Rating	330

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs
REACH SVHC	1.2 - DEHP - Bis(2-ethylhexyl) phthalate (di-2-ethylhexyl phthalate)